



41452089

**SCHUKO soc.out.,mounting orient. var. in 45° steps,screw-in lift term.,R.cl,wh**

**Technical characteristics**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

**Cover, door**

Cover Central cover plate

**Materials**

Colour of labelling 105,105,105

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Material for printing ASA polar white

Surface appearance glossy

Metallic colour No

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with screw-in lift terminals

**Equipment**

Type of configuration Laserdruck

**Use**

---

Differentiation characteristic 2 - Sales	Installation position variable in 45° steps
Differentiation characteristic 3 - Sales	with screw-in lift terminals

---

**Safety**

---

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	without enhanced contact protection
With enhanced contact protection	No

---

**Identification**

---

Main design line	Serie R.classic
------------------	-----------------

---