



41666084

sock. outl. w. earthing cont. USA/CANADA NEMA 5-15 R, Q.x alu velvety, lacq.

Technical characteristics

Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	125 V
Rated voltage	125 V AC
Frequency	50/60 Hz
Rated current	15 A

Dimensions

Insertion depth	19 mm
-----------------	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour	aluminium
Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	velvety

Installation, mounting

Installation mode	without spreader claws, for screw fastening
-------------------	---------------------------------------------

Connection

Type of connection	with screw terminals
--------------------	----------------------

Use

Differentiation characteristic 3 - Sales	with screw terminals
------------------------------------------	----------------------

Standards

Standard	NEMA 5-15 R
----------	-------------

Safety

IK protection code against mechanical impacts	02
-----------------------------------------------	----

Protection

without enhanced contact protection

Identification

Main design line

Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s)

Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

Instructions

Information text

Not UL-certified.