



41666084

sock. outl. w. earthing cont. USA/CANADA NEMA 5-15 R, Q.x alu velvety, lacq.

**Technical characteristics**

**Architecture**

Number of poles 2pole + earth

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 125 V

Rated voltage 125 V AC

Frequency 50/60 Hz

Rated current 15 A

**Dimensions**

Insertion depth 19 mm

**Cover, door**

Cover Central cover plate

**Materials**

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance velvety

**Installation, mounting**

Installation mode without spreader claws ; for screw fastening

**Connection**

Type of connection with screw terminals

**Use**

Differentiation characteristic 3 - Sales with screw terminals

**Standards**

Standard NEMA 5-15 R

**Safety**

IK protection code against mechanical impacts 02

REACH conform Yes

RoHS conform Yes

Halogen free No

Protection without enhanced contact protection

---

**Identification**

Main design line Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s) Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9

---

**Instructions**

Information text Not UL-certified.