



41666086

**Soc.out. earth.contact US/CAN NEMA 5-15 R, screw term., Q.x, ant.velv.lacq.**

#### Technical characteristics

##### Architecture

Number of poles 2pole + earth

##### Configuration

Number of modules 1

##### Main electrical features

Nominal voltage 125 V

Rated voltage 125 V AC

Frequency 50/60 Hz

Rated current 15 A

##### Dimensions

Insertion depth 19 mm

##### Cover, door

Cover Central cover plate

##### Materials

Colour of design line anthracite

Material / workmanship lacquered

Surface appearance velvety

##### Installation, mounting

Installation mode without spreader claws ; for screw fastening

##### Connection

Type of connection with screw terminals

##### Use

Differentiation characteristic 3 - Sales with screw terminals

##### Standards

Standard NEMA 5-15 R

##### Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Protection without enhanced contact protection

<b>Identification</b>	
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
<b>Instructions</b>	
Information text	Not UL-certified.