



41666089

Soc.out. earth. contact USA/CAN NEMA 5-15 R, screw term., Q.x, p.white velv.

Technical characteristics

Architecture

Number of poles 2pole + earth

Configuration

Number of modules 1

Main electrical features

Nominal voltage 125 V

Rated voltage 125 V AC

Frequency 50/60 Hz

Rated current 15 A

Dimensions

Insertion depth 19 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance velvety

Installation, mounting

Installation mode without spreader claws ; for screw fastening

Connection

Type of connection with screw terminals

Use

Differentiation characteristic 3 - Sales with screw terminals

Standards

Standard NEMA 5-15 R

Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Protection without enhanced contact protection

Identification	
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
Instructions	
Information text	Not UL-certified.