



4202

Soc.out. earth. contact+hinged cover US/CAN NEMA 5-15 R,screw, flushmtd IP44

Technical characteristics

Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	125 V
Rated voltage	125 V AC
Frequency	50 Hz
Rated current	15 A

Dimensions

Insertion depth	19 mm
-----------------	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour independent of design lines	white
Colour	white
Colour	white
RAL colour	RAL 1013 - Oyster white
Material	thermoplastic

Installation, mounting

Installation mode	without spreader claws, for screw fastening
-------------------	---

Connection

Type of connection	with screw terminals
--------------------	----------------------

Use

Differentiation characteristic 3 - Sales	with screw terminals
--	----------------------

Standards

Standard	NEMA 5-15 R
----------	-------------

Safety

IK protection code against mechanical impacts	05
Protection	without enhanced contact protection

Identification

Application, usage	Flush-mounted wet-room installation
--------------------	-------------------------------------

Main design line	Splash-protected flush-mounted IP44
------------------	-------------------------------------

Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set.
-------------------	---

Information text	Not UL-certified.
------------------	-------------------