



44713512

**SAF.EMERGENCY push-b. insert, NCcontact+NO contact surf.-/flush-mtd, W.1, grey m.**

#### Technical characteristics

##### Functions

Function	Unlocking by 1/4 rotation
----------	---------------------------

##### Voltage

Rated voltage	240 / 440 V AC
---------------	----------------

##### Electric current

Switching current	10 AX
-------------------	-------

##### Dimensions

Width	71 mm
-------	-------

##### Materials

Material	thermoplastic
----------	---------------

##### Connection

Type of connection	with screw terminals
--------------------	----------------------

##### Safety

Protection index IP	IP20
---------------------	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

##### Use conditions

Operating temperature	-40...30 °C
-----------------------	-------------

Storage/transport temperature	-50...50 °C
-------------------------------	-------------

##### Identification

Main design line	Berker W.1
------------------	------------

##### Instructions

Special note text	Inserts will only reach the degree of protection IP55 if mounted with a housing surface mounted or frame for flush-mounted installation.
-------------------	--

Information text	Pins of quick-release lock made of ZAMAK
------------------	--