



450502

## Loudspeaker soc. out. High End, com-tech

### Technical characteristics

#### Connectivity

Outlet with straight outlet

Connectors / jacks

banana sockets also suitable for screw connection, with 2 metal banana plugs, gold-plated design, with 2 metal banana sockets, gold-plated design

#### Dimensions

Insertion depth 31 mm

#### Resistance

Connect transition resistance < 0.15 mΩ

#### Materials

Material Plastic/metal

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Conductor cross-section max. 10 mm<sup>2</sup>

Clamp transition resistance < 0.1 mΩ

#### Scope of delivery

Component with 2 metal cable lugs, gold-plated design

#### Safety

Protection index IP IP20

REACH conform Yes

RoHS conform Yes

#### Identification

Application, usage Communication technology

Main design line Communication technology

With imprint No

#### Instructions

Information text

Recommendation: use deep box for larger cross-sections. Jack and plug with red or black identification ring, as well as a plug connection are suitable for protection low voltage.