



4539

FCC soc. out., 8 /8-pole, cat.3, com-tech, white

#### Technical characteristics

##### Configuration

Category / ports cat.3

##### Compatibility

For registered plugs RJ 11/12/45

##### Connectivity

Outlet with 45° oblique outlet

Plug type for RJ11, RJ12 and RJ45 plugs

##### Main electrical features

Rated voltage 125 V DC

Rated current 1 A

##### Dimensions

Insertion depth 22 mm

##### Frequency

Transmission bandwidth max. 16 MHz

##### Resistance

Transition resistance < 20 mΩ

##### Materials

Colour independent of design lines white

Colour white

##### Installation, mounting

Installation mode with spreader claws

##### Connection

Type of connection with screw terminals

Cat.3 according to DIN EN 50173

Cat.3 to according to TIA/IAE-568-B.2

##### Cable

Conductor Ø max. 1 mm

##### Safety

Protection index IP IP20

Protection none

**Identification**

---

Application, usage

Communication technology

---

Main design line

Communication technology