



4568

FCC soc. out., 8 (4)-pole, cat.3, com-tech, white

Technical characteristics

Architecture

Design to according to DIN EN 60603-7

Configuration

Category / ports cat.3

Compatibility

For registered plugs RJ 11/12/45

Connectivity

Outlet with 45° oblique outlet

Plug type for RJ11, RJ12 and RJ45 plugs

Main electrical features

Rated voltage 125 V DC

Rated current 1 A

Dimensions

Insertion depth 22 mm

Frequency

Transmission bandwidth max. 16 MHz

Resistance

Transition resistance < 20 mΩ

Materials

Colour independent of design lines white

Colour white

Installation, mounting

Installation mode with spreader claws

Connection

Type of connection with screw terminals

Cat.3 according to DIN EN 50173

Cat.3 to according to TIA/IAE-568-B.2

Cable

Conductor Ø max. 1 mm

Safety

Identification

Application, usage

Communication technology

Main design line

Communication technology