



4584

Modular FCC soc. out. 8/8pole, cat.6A, com-tech

Technical characteristics

Configuration

Category / ports cat.6A, Class EA, unshielded

Connectivity

Outlet with straight outlet

Plug type only suitable for RJ45 plugs

Main electrical features

Rated voltage 72 V DC

Rated current 0.5 A

Voltage

Voltage suitable for PoE+

Dimensions

Insertion depth 35 mm

Frequency

Transmission bandwidth max. 500 MHz

Resistance

Signal contact resistance < 200 mΩ

Materials

Colour code A and B according to TIA/EIA-568-B.2

Material / surface Housing made of ABS

Installation, mounting

Installation mode without spreader claws

Connection

Type of connection with IDC terminals

Standards

real.cat.6a according to DIN IEC 60603-7-51

Safety

Protection index IP IP20

Protection with optional dust protection hinged covers

Use conditions

Operating temperature -40...70 °C

Identification

Application, usage

Communication technology

Main design line

Communication technology