



47063512

SCHUKO soc.out. insert hinged cover surf.-/flushmtd,enhncd contact prot.,W.1,wh.

Technical characteristics

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting or surface-mounting

Main electrical features

Rated voltage	250 V AC
Rated current	16 A

Cover, door

Hinged covers	with hinged cover that falls back, manual clip-in
---------------	---

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Use

Differentiation characteristic 2 - Sales	with enhanced touch protection
--	--------------------------------

Safety

Protection index IP	IP55
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
With enhanced contact protection	Yes

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

Identification

Application, usage	Surface-mounted wet-room installation
Main design line	Berker W.1

Instructions

Special note text	Inserts will only reach the degree of protection IP55 if mounted with a housing surface mounted or frame for flush-mounted installation.
Information text	Pins of quick-release lock made of ZAMAK