



4715

SCHUKO soc. out. hinged cover, splash-protected flush-mtd IP44, white glossy

Technical characteristics

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	30.5 mm
-----------------	---------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour independent of design lines	white
Colour	white
Colour	white
RAL colour	RAL 1013 - Oyster white
Material	thermoplastic
Metallic colour	No

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Safety

IK protection code against mechanical impacts	05
---	----

Protection index IP	IP44
Protection	without enhanced contact protection
With enhanced contact protection	No
Identification	
Application, usage	Flush-mounted wet-room installation
Main design line	Splash-protected flush-mounted IP44
Instructions	
Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set.