



47157002

## Technical characteristics

### Architecture

Design according to DIN 49440

### Configuration

Number of modules 1

### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50 Hz

Rated current 16 A

### Electric current

Rated current 16 A

### Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

### Cover, door

Cover Central cover plate

### Materials

Colour of design line white

Surface appearance glossy

Metallic colour No

### Installation, mounting

Installation mode with spreader claws

### Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

### Safety

IK protection code against mechanical impacts 05

Protection without enhanced contact protection

### Identification

Main design line Berker K.1