



4718

**SCHUKO soc.out. frame+hinged cover, splash-protected flush-mtd IP44, white gl.**

#### Technical characteristics

##### Architecture

|             |                        |
|-------------|------------------------|
| Design      | according to DIN 49440 |
| Fixing mode | flush-mounting         |

##### Configuration

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

##### Main electrical features

|                 |          |
|-----------------|----------|
| Nominal voltage | 250 V    |
| Rated voltage   | 250 V AC |
| Frequency       | 50/60 Hz |
| Rated current   | 16 A     |

##### Electric current

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

##### Dimensions

|                 |       |
|-----------------|-------|
| Insertion depth | 31 mm |
|-----------------|-------|

##### Cover, door

|       |                     |
|-------|---------------------|
| Cover | Central cover plate |
|-------|---------------------|

##### Materials

|                                    |                         |
|------------------------------------|-------------------------|
| Colour independent of design lines | white                   |
| Colour                             | white                   |
| Colour                             | white                   |
| RAL colour                         | RAL 1013 - Oyster white |
| Material                           | thermoplastic           |

##### Installation, mounting

|                   |                     |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

##### Connection

|                      |                          |
|----------------------|--------------------------|
| Connection terminals | according to IEC 60884-1 |
| Connection terminals | according to VDE 0620-1  |
| Type of connection   | with plug-in terminals   |

##### Equipment

|         |                     |
|---------|---------------------|
| Sealing | with sealing flange |
|---------|---------------------|

##### Safety

|   |                                     |
|---|-------------------------------------|
| IK protection code against mechanical impacts | 05                                  |
| Protection index IP                           | IP44                                |
| REACH conform                                 | Yes                                 |
| RoHS conform                                  | Yes                                 |
| Halogen free                                  | No                                  |
| Protection                                    | without enhanced contact protection |
| With enhanced contact protection              | No                                  |

#### Identification

|                    |                                     |
|--------------------|-------------------------------------|
| Application, usage | Flush-mounted wet-room installation |
| Main design line   | Splash-protected flush-mounted IP44 |