



4718

SCHUKO soc.out. frame+hinged cover, splash-protected flush-mtd IP44, white gl.

Technical characteristics

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	31 mm
-----------------	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour independent of design lines	white
Colour	white
Colour	white
RAL colour	RAL 1013 - Oyster white
Material	thermoplastic

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Equipment

Sealing	with sealing flange
---------	---------------------

Safety

IK protection code against mechanical impacts	05
Protection index IP	IP44
Protection	without enhanced contact protection
With enhanced contact protection	No
Identification	
Application, usage	Flush-mounted wet-room installation
Main design line	Splash-protected flush-mounted IP44