



47208982

Combination SCHUKO soc. out. 2gang frame, S.1, white glossy

Technical characteristics

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Special design	special design for Attema
Number of modules	2

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
-----------------	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	white
Colour	white
Colour	white
RAL colour	RAL 1013 - Oyster white
Material	duroplastic

Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Cable

Wiring	2 x 1gang, wired-through
--------	--------------------------

Safety		
IK protection code against mechanical impacts		02
Protection index IP		IP20
REACH conform		Yes
RoHS conform		Yes
Halogen free		Yes
Protection	without enhanced contact protection	
With enhanced contact protection		No

Identification

Main design line	Berker S.1/B.3/B.7
------------------	--------------------