



47228982

**SCHUKO soc. out. cover plate, enhncd contact prot., S.1, white glossy**

**Technical characteristics**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

**Cover, door**

Cover	Full cover plate
-------	------------------

**Materials**

Colour of design line	white
Colour	white
Colour	white
RAL colour	RAL 1013 - Oyster white
Material	duroplastic
Metallic colour	No

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

**Use**

Differentiation characteristic 2 - Sales	with enhanced touch protection
--	--------------------------------

<b>Safety</b>		
IK protection code against mechanical impacts		02
Protection index IP		IP20
REACH conform		Yes
RoHS conform		Yes
Halogen free		No
Protection	Enhanced contact protection	
With enhanced contact protection		Yes
<b>Identification</b>		
Main design line		Berker S.1/B.3/B.7