



47229939

SCHUKO soc. out. cover plate, enhanced contact prot., S.1, al., matt, lacq.

Technical characteristics

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Installation depth, flush-mounted boxes	31 mm
---	-------

Cover, door

Cover	Full cover plate
-------	------------------

Materials

Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	matt
Metallic colour	Yes

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Use

Differentiation characteristic 2 - Sales	with enhanced touch protection
--	--------------------------------

Safety

IK protection code against mechanical impacts	05
---	----

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes
Identification	
Main design line	Berker S.1