



47271606

SCHUKO soc. out. 45°, B.3/B.7, ant., matt

Technical characteristics

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line anthracite

Surface appearance matt

Installation, mounting

Entries for diagonal insertion

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Protection without enhanced contact protection

Identification

Main design line

Berker S.1/B.3/B.7

Secondary design line(s)

Berker S.1 ; Berker B.3 ; Berker B.7

Instructions

Information text

Specially suited for combining several socket outlets
if right angle plugs are used.