



47271909

SCHUKO soc. out. 45°, S.1/B.3/B.7, p. white, matt, plastic

#### Technical characteristics

##### Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

##### Configuration

Number of modules	1
-------------------	---

##### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

##### Electric current

Rated current	16 A
---------------	------

##### Dimensions

Insertion depth	32 mm
-----------------	-------

##### Cover, door

Cover	Central cover plate
-------	---------------------

##### Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Surface appearance	matt

##### Installation, mounting

Entries	for diagonal insertion
Installation mode	with spreader claws

##### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

##### Safety

IK protection code against mechanical impacts	05
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	without enhanced contact protection
With enhanced contact protection	No

#### Identification

Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7

#### Instructions

Information text	Specially suited for combining several socket outlets if right angle plugs are used.
------------------	--