



47272045

SCHUKO soc. out. 45°, R.1/R.3, black glossy

Technical characteristics

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Cover, door

Cover Central cover plate

Materials

Colour of labelling 217,217,217

Colour of design line black

Material for printing PC-PMA black

Surface appearance glossy

Installation, mounting

Entries for diagonal insertion

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Settings

Shading parameter R1_czarny

Laser parameter R1_schwarz

Equipment

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	without enhanced contact protection
With enhanced contact protection	No

Identification

Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1 ; Berker R.3 ; Berker R.8

Instructions

Information text	Specially suited for combining several socket outlets if right angle plugs are used.
------------------	--