



47272089

SCHUKO soc. out. 45°, R.1/R.3, p. white glossy

Technical characteristics

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
-----------------	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Material for printing	ASA polar white

Installation, mounting

Entries	for diagonal insertion
Installation mode	with spreader claws

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Settings

Shading parameter	R1_biały
-------------------	----------

Equipment

Type of configuration	Laserdruck
-----------------------	------------

Safety

Protection index IP	IP20
---------------------	------

Protection	without enhanced contact protection
------------	-------------------------------------

With enhanced contact protection	No
----------------------------------	----

Identification

Main design line	Berker R.1/R.3/R.8
------------------	--------------------

Secondary design line(s)	Berker R.1, Berker R.3, Berker R.8
--------------------------	------------------------------------

Instructions

Information text	Specially suited for combining several socket outlets if right angle plugs are used.
------------------	---