



47276086

**SCHUKO soc. out. 45°, Q.x, ant. velvety, lacq.**

#### Technical characteristics

##### Architecture

Design according to DIN 49440

##### Configuration

Number of modules 1

##### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

##### Electric current

Rated current 16 A

##### Dimensions

Insertion depth 32 mm

##### Cover, door

Cover Central cover plate

##### Materials

Colour of design line anthracite

Material / workmanship lacquered

Surface appearance velvety

##### Installation, mounting

Entries for diagonal insertion

Installation mode with spreader claws

##### Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

##### Safety

IK protection code against mechanical impacts 02

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Protection	without enhanced contact protection
With enhanced contact protection	No
<b>Identification</b>	
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
<b>Instructions</b>	
Information text	Specially suited for combining several socket outlets if right angle plugs are used.