



47387009

**SCHUKO soc. out., enhncd contact prot., K.1, p. white glossy**

**Technical characteristics**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Insertion depth 32 mm

**Cover, door**

Cover Central cover plate

**Materials**

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance glossy

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

**Use**

Differentiation characteristic 1 - Sales with labelling field

Differentiation characteristic 2 - Sales enhanced contact protection

**Safety**

IK protection code against mechanical impacts 05

|                                  |                             |
|----------------------------------|-----------------------------|
| REACH conform                    | Yes                         |
| RoHS conform                     | Yes                         |
| Halogen free                     | Yes                         |
| Protection                       | Enhanced contact protection |
| With enhanced contact protection | Yes                         |

---

**Identification**

|                  |            |
|------------------|------------|
| Main design line | Berker K.1 |
|------------------|------------|

---

**Instructions**

|                  |  |
|------------------|--|
| Information text | Labelling field height arranged for P-touch strips 6 mm. |
|------------------|--|