



47397006

**SCHUKO soc. out., K.1, ant. matt, lacq.**

**Technical characteristics**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Insertion depth	32 mm
-----------------	-------

**Cover, door**

Cover	Central cover plate
-------	---------------------

**Materials**

Colour of design line	anthracite
Colour	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	matt

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

**Use**

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

**Safety**

---

IK protection code against mechanical impacts 05

Protection index IP IP20

Protection without enhanced contact protection

With enhanced contact protection No

**Identification**

---

Main design line Berker K.1

**Instructions**

---

Information text Labelling field height arranged for P-touch strips 6 mm.