



47397009

## SCHUKO soc. out., K.1, p. white glossy

### Technical characteristics

#### Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

#### Electric current

Rated current	16 A
---------------	------

#### Dimensions

Insertion depth	32 mm
-----------------	-------

#### Cover, door

Cover	Central cover plate
-------	---------------------

#### Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic

#### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

#### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

#### Use

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

#### Safety

IK protection code against mechanical impacts	05
Protection index IP	IP20
Protection	without enhanced contact protection
With enhanced contact protection	No

---

**Identification**

Main design line	Berker K.1
------------------	------------

---

**Instructions**

Information text	Labelling field height arranged for P-touch strips 6 mm.
------------------	--