



47397014

**SCHUKO soc. out., K.1, orange glossy**

**Technical characteristics**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Insertion depth 32 mm

**Cover, door**

Cover Central cover plate

**Materials**

Design lines special colours orange

Surface appearance glossy

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

**Use**

Differentiation characteristic 1 - Sales with labelling field

**Safety**

IK protection code against mechanical impacts 05

Halogen free No

Protection without enhanced contact protection

With enhanced contact protection No

---

**Identification**

Main design line

Berker K.1

---

**Instructions**

Information text

Insert colour-coded. 1140. Labelling field height  
designed for 6 mm P-touch strips.