



47397114

**SCHUKO soc. out. "ZSV" imprint, K.1, orange glossy**

**Technical characteristics**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Insertion depth	32 mm
-----------------	-------

**Cover, door**

Cover	Central cover plate
-------	---------------------

**Materials**

Design lines special colours	orange
Colour	orange
Colour	orange
RAL colour	RAL 2003 - Pastel orange
Material	thermoplastic

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

**Use**

Differentiation characteristic 1 - Sales	Labelling field
--	-----------------

**Safety**

IK protection code against mechanical impacts	05
Protection index IP	IP20
Halogen free	No
Protection	without enhanced contact protection
With enhanced contact protection	No

#### Identification

Main design line	Berker K.1
------------------	------------

#### Instructions

Information text	Insert colour-coded. ; Labelling field height arranged for P-touch strips 6 mm.
------------------	---