



47397115

SCHUKO soc. out. "EDV" imprint, K.1, red glossy

Technical characteristics

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
-----------------	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Design lines special colours	red
Colour	red
Colour	red
RAL colour	RAL 3003 - Ruby red
Material	thermoplastic

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Use

Differentiation characteristic 1 - Sales	Labelling field
--	-----------------

Safety

IK protection code against mechanical impacts	05
Protection index IP	IP20
RoHS conform	Yes
Halogen free	No
Protection	without enhanced contact protection
With enhanced contact protection	No

Identification

Main design line	Berker K.1
------------------	------------

Instructions

Information text	Insert colour-coded. ; Labelling field height arranged for P-touch strips 6 mm.
------------------	---