



47403512

SCHUKO soc. out. hinged cover surface-mtd, W.1, p. white, matt, plastic

Technical characteristics

Architecture

Design	according to DIN 49440
Fixing mode	surface-mounting

Configuration

Hollow base	ample room for wiring under the bases of the inserts
Number of modules	1

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Cover, door

Hinged covers	with hinged cover that falls back, manual clip-in
Cover	Complete housing

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Surface appearance	matt
Metallic colour	No

Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

Connection

Conductor cross-section	1...2.5 mm ²
Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1

Terminal with Wago clip-in 2-wire connection terminal for wiring ; with two clip-in places for Wago 2-wire connection terminals in the housing floor

Type of connection	with plug-in terminals
--------------------	------------------------

Cable

Wire

with one entry for 2 cables and one entry for cable
and tube

Equipment

Sealing

with full-face sealing on the rear side of housing for
cable entry and surface adjustment on the backside

Safety

IK protection code against mechanical
impacts

05

Protection index IP

IP55

REACH conform

Yes

RoHS conform

Yes

Halogen free

Yes

Protection

without enhanced contact protection

With enhanced contact protection

No

Use conditions

Operating temperature

-15...30 °C

Storage/transport temperature

-50...50 °C

Identification

Application, usage

Surface-mounted wet-room installation

Main design line

Berker W.1

Instructions

Information text

Hinged cover springs made of stainless steel, pins of
quick-release lock made of ZAMAK