



47413512

SCHUKO soc.out. hinged cover surface-mtd, W.1, p. white, matt, plastic

Technical characteristics

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Rated voltage 250 V AC

Frequency 50 Hz

Rated current 16 A

Cover, door

Hinged covers with hinged cover that falls back, manual clip-in

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Cable

Wire with one entry for 2 cables and one entry for cable and tube

Equipment

Sealing with full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

Use

Differentiation characteristic 1 - Sales with labelling field

Safety

Protection index IP IP55

REACH conform Yes

RoHS conform Yes

Use conditions

Operating temperature -15...30 °C

Storage/transport temperature -50...50 °C

Identification

Application, usage Surface-mounted wet-room installation

Main design line Berker W.1

Instructions

Information text

Labelling field height arranged for P-touch strips 12 mm. ; Hinged cover springs made of stainless steel, pins of quick-release lock made of ZAMAK