



47431404

**SCHUKO soc. out., B.7, al., matt, lacq.**

**Technical characteristics**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Insertion depth 32 mm

**Cover, door**

Cover Central cover plate

**Materials**

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance matt

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

**Safety**

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Protection without enhanced contact protection

With enhanced contact protection No

**Identification**

---

Main design line

Berker S.1/B.3/B.7

---

Secondary design line(s)

Berker S.1 ; Berker B.3 ; Berker B.7