



47432022

## SCHUKO soc. out. "EDV" imprint, R.1/R.3, red glossy

### Technical characteristics

#### Architecture

Design according to DIN 49440

#### Configuration

Number of modules 1

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

#### Electric current

Rated current 16 A

#### Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

#### Cover, door

Cover Central cover plate

#### Materials

Design lines special colours red

Surface appearance glossy

Metallic colour No

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

#### Safety

RoHS conform Yes

Halogen free No

Protection without enhanced contact protection

With enhanced contact protection No

---

**Identification**

Main design line

Berker R.1/R.3/R.8

Secondary design line(s)

Berker R.1 ; Berker R.3 ; Berker R.8

---

**Instructions**

Information text

Insert colour-coded.