



47432045

**SCHUKO soc. out., R.1/R.3, black glossy**

**Technical characteristics**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

**Cover, door**

Cover Central cover plate

**Materials**

Colour of labelling 217,217,217

Colour of design line black

Colour black

Material for printing PC-PMA black

Surface appearance glossy

Metallic colour No

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

**Settings**

Shading parameter R1\_czarny

Laser parameter R1\_schwarz

**Equipment**

---

Type of configuration	Laserdruck
-----------------------	------------

**Safety**

---

REACH conform	Yes
---------------	-----

---

RoHS conform	Yes
--------------	-----

---

Halogen free	Yes
--------------	-----

---

Protection	without enhanced contact protection
------------	-------------------------------------

---

With enhanced contact protection	No
----------------------------------	----

**Identification**

---

Main design line	Berker R.1/R.3/R.8
------------------	--------------------

---

Secondary design line(s)	Berker R.1 ; Berker R.3 ; Berker R.8
--------------------------	--------------------------------------