



47436086

**SCHUKO soc. out., Q.x, ant. velvety, lacq.**

**Technical characteristics**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

**Cover, door**

Cover	Central cover plate
-------	---------------------

**Materials**

Colour of design line	anthracite
Colour	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	duroplastic
Surface appearance	velvety
Metallic colour	No

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

---

**Safety**

IK protection code against mechanical impacts	02
Protection index IP	IP20
Protection	without enhanced contact protection
With enhanced contact protection	No

---

**Identification**

Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9