



47438982

**SCHUKO soc. out., S.1, white glossy**

**Technical characteristics**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

**Cover, door**

Cover Central cover plate

**Materials**

Colour of design line white

Colour white

Colour white

Surface appearance glossy

Metallic colour No

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

**Safety**

IK protection code against mechanical impacts 02

REACH conform Yes

|                                  |                                     |
|----------------------------------|-------------------------------------|
| RoHS conform                     | Yes                                 |
| Halogen free                     | Yes                                 |
| Protection                       | without enhanced contact protection |
| With enhanced contact protection | No                                  |

**Identification**

|                          |                                      |
|--------------------------|--------------------------------------|
| Main design line         | Berker S.1/B.3/B.7                   |
| Secondary design line(s) | Berker S.1 ; Berker B.3 ; Berker B.7 |