



47442045

**SCHUKO soc.out. hinged cover,enhncd contact prot.,var. in 45°step,R.cl**

**Technical characteristics**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Cover, door**

Hinged covers	with self-closing hinged covers
Cover	Central cover plate

**Materials**

Colour of labelling	217,217,217
Colour of design line	black
Colour	black
Colour	deep black
RAL colour	RAL 9005 - Jet black
Material	thermoplastic
Material for printing	PC-PMA black

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

**Settings**

Shading parameter	R1_czarny
Laser parameter	R1_schwarz

**Equipment**

Type of configuration

Laserdruck

**Use**

Differentiation characteristic 2 - Sales

enhanced contact protection

Differentiation characteristic 3 - Sales

Mounting orientation variable in 45° steps

**Safety**

Protection index IP

IP20

Protection

Enhanced contact protection

With enhanced contact protection

Yes

**Identification**

Main design line

Serie R.classic

**Instructions**

Special note text

Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!

Information text

Specially suited for combining several socket outlets if right angle plugs are used.