



47477103

**SCHUKO soc.out. hinged cover,enhncd contact prot.,var. in 45°step,K5 anodised**

**Technical characteristics**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Installation depth, flush-mounted boxes 35 mm

**Cover, door**

Hinged covers when opening hinged cover, it can be arrested in end position

Cover Central cover plate

**Materials**

Colour of design line Aluminium

Material / workmanship aluminium, anodised

Surface appearance matt

Metallic colour Yes

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

**Use**

Differentiation characteristic 2 - Sales enhanced contact protection

Differentiation characteristic 3 - Sales Mounting orientation variable in 45° steps

**Safety**

IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	enhanced contact protection VDE 0620-1
With enhanced contact protection	Yes

**Identification**

Main design line	Berker K.5
------------------	------------

**Instructions**

Information text	Specially suited for combining several socket outlets if right angle plugs are used.
------------------	--