



47477106

SCHUKO soc.out. hinged cover,enhncd contact prot.,var. in 45°step,K1,ant.,

Technical characteristics

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Cover, door

Hinged covers	when opening hinged cover, it can be arrested in end position
Cover	Central cover plate

Materials

Colour of design line	anthracite
Colour	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	matt
Metallic colour	No

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Use

Differentiation characteristic 2 - Sales	enhanced contact protection
--	-----------------------------

Safety

IK protection code against mechanical impacts	05
Protection index IP	IP20
Protection	enhanced contact protection VDE 0620-1
With enhanced contact protection	Yes

Identification

Main design line	Berker K.1
------------------	------------

Instructions

Information text	Specially suited for combining several socket outlets if right angle plugs are used.
------------------	--