



47491606

**SCHUKO soc. out., enhncd contact prot., B.3/B.7, ant., matt**

**Technical characteristics**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Insertion depth 32 mm

**Cover, door**

Cover Central cover plate

**Materials**

Colour of design line anthracite

Surface appearance matt

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

**Use**

Differentiation characteristic 1 - Sales with labelling field

Differentiation characteristic 2 - Sales enhanced contact protection

**Safety**

IK protection code against mechanical impacts 05

REACH conform No

RoHS conform Yes

Halogen free	Yes
Protection	Enhanced contact protection
With enhanced contact protection	Yes

---

**Identification**

Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7

---

**Instructions**

Information text	Labelling field height arranged for P-touch strips 6 mm.
------------------	--