



47516084

## SCHUKO socket outlet with hinged cover, Q.x, alu velvety, lacquered

### Technical characteristics

#### Architecture

|             |                        |
|-------------|------------------------|
| Design      | according to DIN 49440 |
| Fixing mode | flush-mounting         |

#### Configuration

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

#### Main electrical features

|                 |          |
|-----------------|----------|
| Nominal voltage | 250 V    |
| Rated voltage   | 250 V AC |
| Frequency       | 50/60 Hz |
| Rated current   | 16 A     |

#### Electric current

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

#### Cover, door

|               |                                   |
|---------------|-----------------------------------|
| Hinged covers | with hinged cover that falls back |
| Cover         | Central cover plate               |

#### Materials

|                        |                            |
|------------------------|----------------------------|
| Colour                 | aluminium                  |
| Colour                 | aluminium optics           |
| RAL colour             | RAL 9006 - White aluminium |
| Material / workmanship | lacquered                  |
| Material               | thermoplastic              |
| Surface appearance     | velvety                    |
| Metallic colour        | Yes                        |

#### Installation, mounting

|                   |                     |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

#### Connection

|                      |                          |
|----------------------|--------------------------|
| Connection terminals | according to IEC 60884-1 |
| Connection terminals | according to VDE 0620-1  |
| Type of connection   | with plug-in terminals   |

#### Use

|  |                             |
|--|-----------------------------|
| Differentiation characteristic 2 - Sales | enhanced contact protection |
|--|-----------------------------|

#### Safety

|   |                             |
|---|-----------------------------|
| IK protection code against mechanical impacts | 02                          |
| Protection index IP                           | IP20                        |
| Protection                                    | Enhanced contact protection |
| With enhanced contact protection              | Yes                         |

#### Identification

|                          |  |
|--------------------------|--|
| Application, usage       | Flush-mounted wet-room installation            |
| Main design line         | Berker Q.1/Q.3/Q.7/Q.9                         |
| Secondary design line(s) | Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9 |

#### Instructions

|                   |  |
|-------------------|--|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing set (order no. 10107200). |
|-------------------|--|