



47517102

**SCHUKO sock. outl. w. hinged cover a. enhanced cont. protection, K.1, white gl.**

**Technical characteristics**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50 Hz
Rated current	16 A

**Cover, door**

Hinged covers	with hinged cover that falls back
Cover	Central cover plate

**Materials**

Colour of design line	white
Material	thermoplastic
Metallic colour	No

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

**Use**

Differentiation characteristic 2 - Sales	enhanced contact protection
--	-----------------------------

**Safety**

Protection index IP	IP20
Protection	Enhanced contact protection
With enhanced contact protection	Yes

**Identification**

Main design line	Berker K.1
------------------	------------