



47517102

**SCHUKO sock. outl. w. hinged cover a. enhanced cont. protection, K.1, white gl.**

#### Technical characteristics

##### Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

##### Configuration

Number of modules	1
-------------------	---

##### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50 Hz
Rated current	16 A

##### Cover, door

Hinged covers	with hinged cover that falls back
Cover	Central cover plate

##### Materials

Colour of design line	white
Material	thermoplastic
Metallic colour	No

##### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

##### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

##### Use

Differentiation characteristic 2 - Sales	enhanced contact protection
--	-----------------------------

##### Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes

