



47517204

SCHUKO soc.out. hinged cover, enhanced contact prot., K.5, steel, matt finish

Technical characteristics

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Installation depth, flush-mounted boxes	35 mm
---	-------

Cover, door

Hinged covers	with hinged cover that falls back
Cover	Central cover plate

Materials

Colour of design line	Stainless steel
Colour	stainless steel
Colour	stainless steel optics
RAL colour	RAL 9022 - Pearl light grey
Material / workmanship	metal, matt finish
Material	stainless steel
Surface appearance	matt
Metallic colour	Yes

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Use

Differentiation characteristic 2 - Sales

enhanced contact protection

Safety

IK protection code against mechanical impacts

07

Protection index IP

IP20

Protection

enhanced contact protection VDE 0620-1

With enhanced contact protection

Yes

Identification

Application, usage

Flush-mounted wet-room installation

Main design line

Berker K.5

Instructions

Special note text

Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing set (order no. 10107200).