



47527103

SCHUKO soc. out. hinged cover, enhanced contact prot., K.5, al., al. anodised

Technical characteristics

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Cover, door

Hinged covers when opening hinged cover, it can be arrested in end position

Cover Central cover plate

Materials

Colour of design line Aluminium

Material / workmanship aluminium, anodised

Surface appearance matt

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Use

Differentiation characteristic 1 - Sales Labelling field

Differentiation characteristic 2 - Sales enhanced contact protection

Safety

IK protection code against mechanical impacts	07
Halogen free	No
Protection	enhanced contact protection VDE 0620-1
With enhanced contact protection	Yes

Identification

Main design line	Berker K.5
------------------	------------

Instructions

Information text	Labelling field height arranged for 6 mm P-touch strips. Specially suited to combinations of several socket outlets if right angle plugs are used.
------------------	--