



47527104

**SCHUKO soc.out. hinged cover, enhanced contact prot., K.5, steel, matt finish**

**Technical characteristics**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Insertion depth 32 mm

**Cover, door**

Hinged covers when opening hinged cover, it can be arrested in end position

Cover Central cover plate

**Materials**

Colour of design line Stainless steel

Material / workmanship metal, matt finish

Surface appearance matt

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

**Use**

Differentiation characteristic 1 - Sales Labelling field

Differentiation characteristic 2 - Sales enhanced contact protection

**Safety**

IK protection code against mechanical impacts	07
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes

**Identification**

Main design line	Berker K.5
------------------	------------

**Instructions**

Information text	Labelling field height arranged for 6 mm P-touch strips. Specially suited to combinations of several socket outlets if right angle plugs are used.
------------------	--