



47527203

SCHUKO soc. out. hinged cover, enhanced contact prot., K.5, al., al. anodised

Technical characteristics

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
-----------------	-------

Cover, door

Hinged covers	with self-closing hinged covers
Cover	Central cover plate

Materials

Colour of design line	Aluminium
Colour	aluminium
Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material / workmanship	aluminium, anodised
Material	Aluminium
Surface appearance	matt

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Use

Differentiation characteristic 1 - Sales	Labelling field
Differentiation characteristic 2 - Sales	enhanced contact protection
Safety	
IK protection code against mechanical impacts	07
Protection index IP	IP44
Halogen free	No
Protection	enhanced contact protection VDE 0620-1
With enhanced contact protection	Yes
Identification	
Application, usage	Flush-mounted wet-room installation
Main design line	Berker K.5
Instructions	
Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing set (order no. 10107200).
Information text	Labelling field height arranged for 6 mm P-touch strips. Specially suited to combinations of several socket outlets if right angle plugs are used.