



47527204

SCHUKO soc.out. hinged cover, enhanced contact prot., K.5, steel, matt finish

Technical characteristics

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Cover, door

Hinged covers with self-closing hinged covers

Cover Central cover plate

Materials

Colour of design line Stainless steel

Material / workmanship metal, matt finish

Surface appearance matt

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Use

Differentiation characteristic 1 - Sales Labelling field

Differentiation characteristic 2 - Sales enhanced contact protection

Safety

IK protection code against mechanical impacts 07

Protection index IP	IP44
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes

Identification

Application, usage	Flush-mounted wet-room installation
Main design line	Berker K.5

Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing set (order no. 10107200).
Information text	Labelling field height arranged for 6 mm P-touch strips. Specially suited to combinations of several socket outlets if right angle plugs are used.