



47537009

**Double SCHUKO soc. out. cover plate, K.1, p. white glossy**

**Technical characteristics**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	2
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Assembling height	22 mm
-------------------	-------

**Cover, door**

Cover	Full cover plate
-------	------------------

**Materials**

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic

**Installation, mounting**

For installation in 1gang wall boxes	according to DIN 49073-1
Installation mode	with spreader claws

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

**Safety**

Protection index IP	IP20
Protection	without enhanced contact protection

